

# **Automated Inventory Management**Small RFID Refrigerator: TC-197

TrackCore Operating Room, the industry leading tissue and implant management software, integrates with intelligent RFID-enabled enclosures to automate your chain of custody and inventory management without human intervention.

AUTOMATE CHAIN OF CUSTODY TRACKING

IMPROVE REGULATORY COMPLIANCE

ABSOLUTE ACCOUNTABILITY

INVENTORY OPTIMIZATION



#### HOW RFID TECHNOLOGY WORKS

#### ONE

Place the internet-enabled RFID enclosure at the point of use.

#### TWO

Pre-authorized users are able to access the enclosure with RFID-enabled badges.

## THREE

Users can then add or remove RFID-tagged inventory from the enclosure.

### FOUR

The user, items added or removed, date/time, and temperature are all automatically tracked.



trackcoreinc.com



616.632.2222



sales@trackcoreinc.com

CONFIDENTIAL: This document is intended only for the original recipient. The information contained herein is confidential and may constitute inside or non-public information under international, federal, or state securities laws. Unauthorized forwarding, printing, copying, distribution or use of such information is strictly prohibited and may be unlawful. Please contact TrackCore, Inc. at +1.616.632.2222.



### TC-197 | Small RFID Refrigerator | 4.6 ft³ Intelligent Refrigerator

#### **DETAILS AND DIMENSIONS**

COMPONENT	SPECIFICATION	
External Dimensions	34"H × 23.75"W × 24.5"D	
Internal Dimensions	23.5"H x 17.5"W x 17"D	
External Clearance	< 1" on sides, 1" on rear	
Volume	4.6 ft³	
Weight	130 lbs	
Temperature Range	perature Range + 1° C to + 10° C	
Temperature Uniformity	+/- 1° C	
Door	Solid, right hand hinge	
Security Device	Electronic door lock	
Access Control	LF pass reader	
Refrigerant	R600a (SNAP)	
Cooling Method	Forced Air Cooled	
Defrost Type	Automatic	



COMMUNICATION	SPECIFICATION	POWER	SPECIFICATION
RFID Frequencies	902 to 928 MHz	Electrical Power	120 VAC, 60 Hz, 2 A
	Ethernet, optional	Plug Type	NEMA 5-15
	cellular	Power Consumption	1.15k Wh/day
		RFID Battery Backup	24VDC, 1.3Ah sealed lead acid